


Worcester Controls C44 Cryogenic 3-Piece Ball Valves



Experience In Motion








Contents

Overview
Parts/Materials4
Valve Dimensions5
Throttling Control of Cryogenics 6
Other Cryogenic Products7



Cryogenic Valve Design

Flowserve Worcester's experience and expertise in the design of cryogenic ball valves has been recognised throughout the process industry for over 30 years. Utilising a combination of our Fluorofill seat material and our unique 'S' gasket body seal, the valve provides positive shut-off in the most demanding of cryogenic applications. From the original C44 R5 and MC44 designs the seat and body seals have remained a constant feature and with both products now rationalised into the C44 R7, additional technical advantages have been included to provide what is considered the best cryogenic ball valve on the market.

The Worcester 3-piece ball valve offers a number of technical advantages over other types of valve.

Tested and certified to EN1626 and can be used on TPED CATIII applications.

High Flow Rate

The high Cv available from a ball valve compared with a globe valve makes the C44 ideal for loading stations where speed of delivery is critical. The valve is also available as fullbore up to DN40 as the C59 series.

Low Body Mass


The one-piece design minimises the mass of the body and therefore makes the valve economic to use. It also provides a weight advantage, making the valve ideal for road tankers and other transportation requirements.

Ease of Operation


The unique low torque seat design and the 90 degree operation of the ball valve makes it ideal for use with both pneumatic and electric actuators with the additional benefit of rotary control if required. When manually operated, the lever provides visual indication of the valve orientation (open or closed) which is critical in the safe loading and unloading of liquid gases.

Ease of Maintenance

The 3-piece concept provides the benefit of easy maintenance through the "slide out" body method.








Parts/Materials List

ITEM	DESCRIPTION	MATERIAL	ITEM	DESCRIPTION	MATERIAL
1.	Body	Stainless Steel ASTM A351/CF3M	12.	Split Thrust Bearing (Halves)	Polyfill
		Brass ASTM B283 C37700	13.	Split Ring (Halves)	Stainless Steel ASTM A479/316L
2.	Extension	Stainless Steel ASTM A312/316L	14.	Belleville Washer	Stainless Steel AISI 301
3.	Bonnet Plate	Stainless Steel ASTM A743/CF3M	15.	Spring Washer	Stainless Steel AISI 300 Series
4.	Pipe End	Stainless Steel ASTM A351/CF3M Brass BS2872 CZ122	16.	Stem & Wrench Nut	Stainless Steel AISI 300 Series/Zinc Plated
5.	Ball	Stainless Steel ASTM A479/316 Cond. A	17.	Body Nut	Stainless Steel ASTM A194 Gr.8
6.	Stem Assembly	Stainless Steel ASTM A479/316 Cond. A	18.	Body Bolt	Stainless Steel ASTM A193 Gr.B8/ENP
7.	Seat	Fluorofill	19.	Thrust Bearing	Fluorofill
8.	Body Seal	Stainless Steel AISI 316/TFE Coated	20.	Nameplate	Stainless Steel AISI 304
9.	Packing Follower (Bottom)	Stainless Steel ASTM A479/316L	21.	Wrench/Sleeve Assembly	St. Steel AISI 300 Series/Vinyl Coated
10.	Packing Ring	Crane Chemlon V-Ring/Teflon	22.	Stop Pin	Stainless Steel AISI 300 Series
11.	Packing Follower (Top)	Stainless Steel ASTM A479/316L	23.	Locking Clip	Carbon Steel Plated




<u>5</u>



Throttling Control of Cryogenics


The Worcester V-Flow provides positive shut-off with accurate control by utilising a cryogenic flourofill seat downstream and a metal profiled seat upstream. The choice of seat profile on the upstream seat is dependent on the flow conditions required. The V-Flow is ideally suited for either electric actuation using a 75 series Norbro DataFlo P or pneumatic 40R series with a PMV positioner.

The combination of the V-Flow with the cryogenic C44 design provides an ideal cryogenic control valve for a variety of applications from food freezing to high purity gases.






Flow Characteristic Options



CF51/52	For petrochemical requirements the CF51/52 firesafe cryogenic valve is	
Elg.	available utilising the same ball and seats as used in the C44 valve.	
DC13	Using the C44 concept for diverting flow, the DC13 is a 90 degree operation valve.	
CB18	The cryogenic version of our B18 provides a true multi-port design.	
VC44	For control of liquid gases the VC44 valve utilises the profiled metal seat from the proven V-Flow control valve (see p6).	
CN44	For non-continuous cryogenic applications, the CN44 (non-extended) is ideal for drains on cryogenic lines. The valve contains the same ball, seats and body seals as the C44.	
C59	The cryogenic valve is also available as full bore up to 40mm bore for applications where high flow rates are required.	





Standards of Compliance

Butt Weld Valves	Weld Preparation:		
	SCH 40 & 10: BS 2633 suitable		
	for Schedule Pipe to BS 1600		
Socket Weld Valves	Prepared for assembly to plain end pipe in		
	accordance with BS 1600		
Screwed Valves	Threaded Specification:		
	BSP Taper - BS21/ EN 10226-1		
	BSP Parallel - ISO 228/1		
	NPT - ASNI B1.20.1		
Test Rating	Valves are subjected to the requirements of		
	EN 12266-1		
	EN1626 (Valves for Cryogenic service)		

Typical Applications

- Road tankers
- Terminal unloading stations •
- Food freezing systems
- High purity cryogenic gas systems •
- Steel production plants •
- LN₂ and CO₂ storage vessels
- and many other services and applications

FCD WCEBR0013-02 Printed in Germany. (Replaces PB06 Rev 11/02)

To find your local Flowserve representative:

For more information about Flowserve Corporation, visit www.flowserve.com or call USA 1 800 225 6989

Due to continuous development of our product range, we reserve the right to alter the dimensions and information contained in this leaflet as required Information given in this leaflet is made in good faith and based upon specific testing but does not, however, constitute a guarantee.

Notes

- 1. Screwed, butt weld and socket weld variations are available.
- 2. When wrench not fitted, flats on stem, when parallel to pipeline axis, denote ball open.
- 3. All weld end valves are assembled with 'S' gasket ring body connector seals with additional seals attached loose. This provides for the valve to be tested by Worcester Controls, disassembled by the customer to weld inline, and reassembled-Instructions will be supplied for fitting body seals.
- 4. All valves are built in a clean room and are suitable for oxygen service.
- 5. Installation. Operating and Maintenance Instructions supplied with the product and are also available on request.
- 6. Installation. Stem to be installed 45° max from vertical.

Technical Information

Valve Size		fficients	Equivalent Length of Pipe		
in	Cv	Kv	Feet	Metres	
1⁄4-1⁄2	8.3	7.2	1.9	0.58	
3⁄4	13.6	11.8	5.5	1.67	
1	37.5	32.6	3.0	0.91	
1¼	37.7	32.7	4.6	1.4	
1½	79.5	69.1	3.9	1.19	
2	106	92	9.0	2.28	
	in 1/4-1/2 3/4 1 11/4 11/2	in Cv ¼-½ 8.3 ¾ 13.6 1 37.5 1¼ 37.7 1½ 79.5	in Cv Kv ½-½ 8.3 7.2 ¾ 13.6 11.8 1 37.5 32.6 1¼ 37.7 32.7 1½ 79.5 69.1	in Cv Kv Feet ½-½ 8.3 7.2 1.9 ¾ 13.6 11.8 5.5 1 37.5 32.6 3.0 1¼ 37.7 32.7 4.6 1½ 79.5 69.1 3.9	

Cv - Flow in US GPM Pressure - psi Kv - Flow in M3/hr Pressure - bar



ſ

All valves are built in the clean room and are suitable for oxygen service.

Flowserve Flow Control

A Division of Flowserve GB Ltd Burrell Road, Haywards Heath West Sussex RH16 1TL United Kingdom Telephone: +44 (0)1444 314400 Telefax: +44 (0)1444 314401 Email: wvukinfo@flowserve.com

flowserve.com